

Master-Core Basic

Developed with Dr. Istvan Urban

Das Master-Core Basic dient der einfachen und sicheren Gewinnung von Knochenzylindern im Rahmen der Knochenaugmentation. Dazu enthält das System Trepane mit unterschiedlichen Längen und Durchmessern. Aufgrund der unterschiedlichen Längen verfügen die Trepane dabei über eine automatische Tiefenbegrenzung, was für den Schutz anatomischer Strukturen sorgt und damit eine besonders sichere und kontrollierte Knochenentnahme erlaubt. Darüber hinaus ermöglichen Tiefenmarkierungen an den Arbeitsteilen eine zusätzliche Tiefenkontrolle während der Extraktion. Die schwarze Beschichtung der Trepane erlaubt dabei blendfreies Arbeiten und die optimale Sichtbarkeit der Tiefenmarkierungen.

The Master-Core Basic is used for the simple and safe extraction of bone cylinders in the context of bone augmentation. For this purpose, the system contains trepanes with different lengths and diameters. Due to the different lengths, the trepanes have an automatic depth stop, which ensures the protection of anatomical structures and thus allows for a particularly safe and controlled bone extraction. In addition, depth markings on the trepanes' working parts enable additional depth control during the extraction. The black coating of the trepanes allows for glare-free work and the optimal visibility of the depth markings.



Master-Line
by
Dr. Istvan Urban

Art.-No. BMCBA

AUF EINEN BLICK

- Einfache und sichere Gewinnung von Knochenzylindern
- Optimaler Schutz anatomischer Strukturen dank tiefenbegrenzter Trepane
- Tiefenmarkierung an den Trepanen zur zusätzlichen Tiefenkontrolle
- Extraktion von Knochenzylindern unterschiedlicher Durchmesser und Längen
- Schwarze Beschichtung der Trepane für blendfreies Arbeiten

AT A GLANCE

- Simple and safe extraction of bone cylinders
- Optimal protection of anatomical structures thanks to depth-limited trepanes
- Depth markings on the trepanes for additional depth control
- Extraction of bone cylinders of different diameters and lengths
- Black coating on the trepanes for glare-free work

	Vorkörner Trepane Initial bur Trepanes	Bohrerverlängerung Drill Extension
Fig.	DV229	BV025
Shank ¹	204	205
Size ²	050	-
Length mm	2.0	25.5
mm	5.0	-
mm	5.7	-

¹ 204=RA, 205=RA L

² Größter Arbeitsteildurchmesser in 1/10 mm² Largest working part diameter in 1/10 mm

mm Innendurchmesser Internal diameter mm Außendurchmesser External diameter

	Trepane Trephines									
										
Fig.	229IU	229IU	229IU	229IU	229IU	229IU	229IU	229IU	229IU	229IU
Shank ¹	206	206	206	206	206	206	206	206	206	206
Size ²	603	604	605	606	607	803	804	805	806	807
Length mm	3.0	4.0	5.0	6.0	7.0	3.0	4.0	5.0	6.0	7.0
 mm	5.0	5.0	5.0	5.0	5.0	7.0	7.0	7.0	7.0	7.0
 mm	6.0	6.0	6.0	6.0	6.0	8.0	8.0	8.0	8.0	8.0

¹ 206=RA XL

² Größter Arbeitsteildurchmesser in 1/10 mm² Largest working part diameter in 1/10 mm

mm Innendurchmesser Internal diameter mm Außendurchmesser External diameter